

Features

- **Secure Collection** – Equipped with a cam lock to protect and secure submitted comments or suggestions.
- **Durable Build** – Constructed from solid **steel sheets** for long-term reliability in industrial environments.
- **Front Pocket Convenience** – Integrated pocket to hold suggestion slips and writing instruments for user ease.
- **Customizable Finish** – Available with **powder coating or custom printing** as per client specifications.
- **Highly Visible** – Standard **bright yellow color** ensures the box is easily identifiable in workplace settings.
- **Confidential Feedback** – Designed to protect the privacy of submissions from employees, customers, or visitors.

Product Description

RS PRO Lockout Suggestion Box

RS Stock No.: 0694378



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Suggestion Box (or Comment Box) provides an effective way to collect valuable comments or suggestions from employees, customers, or visitors.*
- *Built from durable steel sheets with a lockable cam mechanism, it ensures secure and confidential storage of contents.*
- *Lock Type: Security cam lock with two keys*
- *Features a front pocket for keeping suggestion slips and pens accessible to users.*
- *Yellow colour powder coated finish, ensuring visibility and recognition in the workplace.*
- *Ideal for promoting employee engagement, safety improvements, and workplace communication.*
- *Suitable for wall mounting in common areas, break rooms, or near LOTO stations to encourage regular feedback. Mounting hardware included.*

General Specifications

Type	Suggestion Box
Material	Galvanized steel with powder-coated finish
Colour	Yellow
Package	BOPP + Box

Mechanical Specifications

Dimensions	257mm (H) x 229mm (W) x 129mm (D)
Height	257mm
Width	229mm
Depth	129mm
Weight	1.85 kg

Operation Environment Specifications

Withstand temperature	-20°C - 175°C
------------------------------	---------------