



Prism Pro CCT Fire Rated Gimbal Satin Chrome



- 220-240V IP20 dimmable LED 4 CCT selectable fire rated performance gimbal suitable for residential and hospitality applications
- 30° tilt angle
- Remote driver with 2x1.5mm² + CPC loop-in, loop-out colour coded push fit piano terminals provide an easy and efficient installation
- Detachable LED driver for fast fix install
- Low profile design and remote driver allows installation into shallow ceiling voids
- Fully tested for 30, 60 and 90 minute ceiling types to meet Part B of building regulations
- Fully tested to meet Part E (acoustic) and Part L (energy) of Building Regulations
- Wide 60° beam angle for increased light distribution

General Information

| | |
|---------------------|----------|
| Lamp Type | LED |
| Dimmable | Yes |
| Fire Rated | Yes |
| IP Rating | IP20 |
| Class Protection | 2 |
| Internal / External | Internal |



| | |
|--------------------------------|------------------------------------|
| Surface / Recessed / Suspended | Recessed |
| OCTO Category | OCTO compatible powered by Casambi |
| Bluetooth Enabled | Yes |
| Warranty (Years) | 5 |
| Material | Aluminium, Polycarbonate |
| Technical Information | |
| Wattage | 7W |
| Lumens Delivered | 700lm (4000K) |
| Lm/W | 100lm/W (4000K) |
| Beam Angle | 60 |
| CRI | 80 |
| CCT | 2700/3000/4000/6000K |
| Input | 220/240V |
| Hertz | 50/60Hz |
| Operating Temp | -5°C to 25°C |
| Lumen Depreciation | L70 60,000h |
| Power Factor | 0.9 |



