



1. THIS PLUG IS DESIGNED TO CONFORM TO THE LATEST ISSUE OF MIL-C-24308
 2. MAX WIRE INSUL. TO BE USED WITH THIS PLUG IS .054 DIA.
 3. METAL RETENTION CLIPS ARE INCLUDED IN INSERTS
 4. PACKAGE MARKED M24308/4-269F
 5. THIS PLUG WILL ACCEPT SIZE 22 PIN CONTACT M 39029/58-360 OR ANY AMP HDD-22 PIN CONTACT
- △ AMP PART NO. MARKED ON CONNECTOR REPRESENTS KIT NUMBER WITH CONTACTS
- △ UL/CSA DESIGNATION MARKED IN THIS AREA. OPTIONAL

OBSELETE	STEEL, CLASS G	PHENOLIC COLOR: BLACK	204511-3
SUPSD BY 206066-4	BRASS	DIALYL PATHALATE COLOR: BLUE	204511-2
	STEEL, CLASS G	DIALYL PATHALATE COLOR: BLUE	204511-1
	SHELL MAT'L	INSERT MAT'L	INSERT MAT'L

THIS DRAWING IS A CONTROLLED DOCUMENT. DWN: C.C.THOMAS 12-2-87
 OK: F.C.BALLEW III 1-25-88

Tyco Electronics Corporation
 Harrisburg, Pa 17105-3608

NAME: AMPLIMITE PLUG FOR PIN CONTACTS
 HI-DENSITY D CONNECTOR
 SIZE 6 (104 POSN) SERIES 90

SIZE: A1 CAGE CODE: 00779 DRAWING NO: 204511

RESTRICTED TO: CUSTOMER DRAWING

SCALE: 4:1 SHEET: 1 OF 1 REV: U