

## 19 IMU-10

### 1/2" Socket set

27 pieces

Code  
6139750

ETIM  
EC002209

EAN  
4010886613979

UNSPSC  
27-11-17-03

Country of origin  
Germany

eCl@ss  
21-04-02-05

Customs tariff number  
82042000



### Article description

- With forged, tempered hexagon (No. 19) or bi-hexagon (No. D 19) UD profile sockets, hand-operated
- With accessories made from vanadium steel 31CrV3
- With robust lever-change reversible ratchet, with push-button release
- In GEDORE blue sheet steel case
- Dimensions: 425 x 277 x 55 mm

### Article parts list

Ratchet, 1993 U-10 T, Inserts, 19 10 11 12 13 14, 15 17 19 22 24 27 30, IN 19 5 6 7 8 10 12 14, 15 19 8 10, ICS 19 2 3, Accessories, 1/2" extension 1990-5-10, Cardan joint 1995

### Article information

Contents (Qty of pieces)	27	Total height [mm]	57 mm
Net weight [kg]	6,9 kg	Total depth [mm]	277 mm
Total length [mm]	425 mm	Drive connector square (male)	1/2"
Total width [mm]	280 mm	Drive connector square (male)	12,5 mm