

1100-278801

## Manual bending tool set in L-BOXX® 136

in GEDORE L-BOXX® 136, 16 pieces

Code	ETIM
2963515	EC002189
EAN	UNSPSC
4017981012447	27-11-25-01
Country of origin	eCl@ss
Spain	21-04-16-03
Customs tariff number	
82055980	



## Article description

- Sizes from 3 to 18 mm to 180°
- Use:
  - Precision steel pipes EN 10305-3 (DIN 2394)
  - Hydraulic pipes EN 10305-1 (DIN 2391) with 1.0 - 2.0 mm wall thicknesses
  - Composite pipes up to 16 mm
  - Bendable stainless steel tubes with wall thicknesses from 1.0 - 1.5 mm
- With 10 aluminium bending formers for pipes with  $\varnothing$  3-4, 5, 6, 8, 10, 12, 14, 15, 16 and 18 mm
- For clamping in a vice
- Can be used as bending pliers up to size 10 mm
- As from sizes 12 mm also for stationary use with tripod No. 268500
- With pipe cutter No. 2180 3
- In GEDORE L-BOXX® 136 No. 1100 L
- Dimensions: W 442 x D 357 x H 151 mm

## Article parts list

1 basic frame 3-10 mm No. 278570, 1 bending lever 3-10 mm No. 278581, 1 basic frame 6-18 mm No. 278670, 1 bending lever 6-18 mm attachable No. 278680, 10 aluminium bending formers for pipes with  $\varnothing$  3-4, 5, 6, 8, 10, 12, 14, 15, 16, 18 mm, 1 pipe cutter 3-35 mm  $\varnothing$  No. 2180 3, 1 pin punch 3 mm, + GEDORE L-BOXX® 136 No. 1100 L

## Article information

Contents (Qty of pieces)	1	Total width [mm]	442 mm
Net weight [kg]	8,72 kg	Total height [mm]	151 mm
Total length [mm]	357 mm		