

## 400 36X41

### Double ended ring spanner

open

Code 1933175 ETIM EC002188  
 EAN 4010886865811 UNSPSC 27-11-17-05  
 Country of origin Germany eCl@ss 21-04-01-06  
 Customs tariff number 82041100



### Article description

- Acc. to DIN 3118
- Sizes 8x10 to 12x14 mm with hexagon
- Vanadium steel 31CrV3, chrome-plated
- Application on hydraulic/brake lines
- Use:
- Heads 15° angled
- Hexagonal opening 30° offset, UD profile opening 15° offset

### Article information

Contents (Qty of pieces)	1	Width of head 2 [mm]	66 mm
Version/Execution	Heads 15° angled hexagonal Opening 30° offset, UD profile Opening 15° offset	Head height 2 [mm]	28,2 mm
Net weight [kg]	0,98 kg	Head height 1 [mm]	25,2 mm
Total length [mm]	345 mm	Width of head 1 [mm]	58,0 mm
Total width [mm]	65 mm	Width across flats [mm]	36x41
Total height [mm]	38 mm	Width across flats 2 [mm]	41
Surface	chrome-plated	Ring profile	UNIT-DRIVE
Use	Application on hydraulic/brake lines	Opening width 1 (min.) [mm]	25,0 mm
Material	31CrV3	Opening width 2 (max.) [mm]	32,0 mm
Standard	DIN 3118	Weight	2,160 lbs
Width across flats 1 [mm]	36	Ring angle	15°