



Nokia 6303 classic Data Sheet

Planned Market Introduction

- Q2 2009

Category

- Connect

Key Features:

- Elegant design in durable stainless steel with all the essentials
- Great talk-time: Up to 7 hours talk time, more than 2½ weeks on stand-by
- Enjoy the 2,2" QVGA display supporting 16.7 million true colors
- Capture high quality pictures with the 3.2 megapixel auto focus camera and dual LED flash
- Easy to share pictures through favorite sharing sites like Share on Ovi or via MMS and e-mail.

Additional Features:

- Great music: the Nokia 6303 classic comes with FM radio and MP3 player, and supports the 3,5mm AV
- Nokia Maps are pre-loaded to ensure fast and easy access to maps applications.
- Nokia Web Browser
- Instant messaging
- Support for 4GB microSD memory card, 1GB microSD memory card inbox

Photo and Video:

- 3.2 megapixel camera, 8x digital zoom, autofocus
- Photo and video sharing online

Available Nokia Original Accessories:

- Headsets:** Nokia Stereo Headset WH-102
Nokia Bluetooth Headset BH-600
Nokia Bluetooth Headset BH-606
Nokia Bluetooth Headset BH-900
- Data:** Nokia Connectivity Cable CA-101D
Nokia 1GB microSD Card (with Nokia Maps preloaded)
Nokia 4GB microSD Card
- Power:** Nokia Travel Charger AC-8
Nokia Battery BL-5CT
- Car solutions:** Nokia Universal Charging Holder CR-8
Nokia Bluetooth Display Car Kit CK 100
- Navigation solution:** Bluetooth GPS Module LD-4W

Technical Profile:

- System:** EGSM 900/1800/1900 MHz
- User Interface:** S40
- Dimensions:** 108.8 x 46.2 x 11.7 mm (L x W x T)
- Weight:** 96 g
- Display:** 2.2 inch QVGA (320 x 240 pixels) with up to 16.7 million colors
- Battery:** Nokia Battery BL-5CT, 1050 mAh
- Memory:** Up to 17 MB internal memory, support for up to 4GB microSD memory card

Main Camera:

- Image capture:** 3.2 megapixels
- Video capture:** MPEG-4 VGA at up to 15 fps
- Flash:** Dual led flash

Operating Times:

- Talk time:** Up to 7.0 hours
- Standby time:** Up to 450 hrs
- Music playback:** Up to 15 hours

Data Services & Connectivity:

- Tri-band; EGSM 900/1800/1900
- Micro-USB connector
- 3.5 mm AV connector
- Small DC charger plug
- Bluetooth