

Datasheet

ECP-15 Euro series

15W plug-in power supply



Features

- Input Voltage: 90 – 264Vac
- Output Power: 15W
- No Load power consumption
- UK and European versions available
- Compact and light-weight plastic case
- Protections: short circuit/overload/ overheat
- 1 year warranty
- Dimensions: 70mm x 60mm x 50mm
- Connector: 2.1 x 5.5 x 9.5mm
- Weight: 147g

Part number	Voltage	Rated Current	Voltage range	Line Regulation	Load Regulation	Ripple and Noise	MTBF
726-2810	5V	3A	4.7 ~ 5.3V	± 1%	± 5%	<10%	100,000hrs min. MIL-HDBK – 217F (25°C)
726-2814	7.5V	2A	7.1 ~ 7.9V				
726-2823	9V	1.67A	8.5 ~ 9.5V				
726-2826	12V	1.25A	11.4 ~ 12.6V				
726-2820	15V	1A	14.25 ~ 15.75V				
726-2839	18V	0.83A	17.1 ~ 18.9V				
726-2832	24V	0.63A	22.8 ~ 25.2V				

Mechanical specification

