

#### **FEATURES**

- Waterproof IP68
  rating guarantees
  protection against
  extended immersion
  under higher
  pressures
- Cable out diameter range of 7 mm to 12 mm
- Gold-plated brass contacts for corrosion resistance
- Threaded mating type
- Operating temperature range from -25.0°C to 85°C
- 5 brass contacts
- Polymer housing
- Screw termination
- Conforms to standards ANSI/ESD S20.20:2014 and BS EN 61340-5-1:2007

# RS PRO Screw Circular Connector, 5 Contacts, Cable Mount, IP68

RS Stock No.: 124-6694



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



#### **Product Description**

RS PRO 5-position circular connectors offer a quick and reliable way to secure wire connections for both cable-to-cable and cable-to-panel applications.

Also, this product is equivalent to 124-6688 Plug + 124-6666 Socket.

#### **General Specifications**

Number of Contacts	5
Housing Material	Polymer
Contact Material	Brass
Contact Plating	Gold
Pole Format	5P
Contact Gender	Female, Male
Mating Type	Threaded
Body Orientation	Straight
Mating Cycles	>500
Shell material	Nylon66, fire resistance: V-0
Colour	Black/Blue
Application	Marine, Automotive

# **Electrical Specifications**

Plug/Socket	Plug, Socket
Current Rating	25.0A
Voltage Rating	500.0 V
Insulation Resistance	2000ΜΩ



## **Mechanical Specifications**

Connector Size	Standard
Termination Method	Screw
Mounting Type	Cable Mount
Panel Cut-Out	21mm
Contact Diameter	7mm to12mm

# **Operation Environment Specifications**

Operating Temperature	-25°C to 85°C

## **Protection Category**

IP Rating	IP68

#### **Approvals**

Compliance/Certifications	ANSI/ESD S20.20:2014, BS EN 61340-5-1:2007



# **Industrial Circular Connectors**



