



FACK2SBpm



FACK4Bpm



FKFBpm



KBNC1275BPM



KBNC50Bpm



KCF3GBpm



KCHDBpm



KCK66Bpm



KCUAA2Bpm



KCUABBpm



KOLADXBpm



KOLMMDXBpm



KOLSMDXBpm



KSH66Bpm



SACK3SBpm



SACK4Bpm



SEKjeBpm



SGACK2SBpm



SGACK902SBpm



SGKSjeBpm



SGKSLJBpm



SKFBpm



SKmcBpm



SLJBpm



SGKctBpm



KAPMBfml



KAPMkpk



KAPMkpk2



SGACK90Bpm



SGKSbtBpm



FFPM16MC



FFPM16



KUCC20Bpm



KCUAB3Bpm



Code	Description	Dimensions - Weight (L x W x H mm)	Link to Keystone's Specification	EAN Numbers
FAK2SBpm	Category 5e female to female coupler, shielded	29.7 x 19 x 35 – 19.5g	<a href="#">FAK2S</a>	5055386509390
FAK4Bpm	Category 5e unshielded compact coupler	29.5 x 19 x 35 – 8.5g	<a href="#">FAK4</a>	5055386509406
FKFBpm	Category 5e tool-less IDC socket, unshielded	37 x 19 x 35 – 8.5g	<a href="#">FKF</a>	5055386509413
KBNC1275Bpm	BNC coupler Ultra HD 75 ohm 12Ghz	32.5 x 19 x 35 – 12.5g	<a href="#">KBNC1275</a>	5055386509468
KBNC50Bpm	BNC 50-ohm female to female coupler	32.5 x 19 x 35 – 18.5g	<a href="#">KBNC50</a>	5055386509475
KCF3GBpm	3G F connector female to female coupler	25.5 x 19 x 35 – 8.5g	<a href="#">KCF3G</a>	5055386509857
KCHDBpm	HDMI female to female coupler	19.8 x 19 x 35 – 10.5g	<a href="#">KCHD</a>	5055386509482
KCK66Bpm	RJ12 6p6c coupler	26.5 x 19 x 35 – 6.5g	<a href="#">KCK66BKne</a>	5055386509703
KCUAA2Bpm	USB2 A female to A female coupler	35.5 x 19 x 35 – 10.5g	<a href="#">KCUAA2</a>	5055386509499
KCUABBpm	USB2 A female to B female adaptor, reversible	34.4 x 19 x 35 – 10.5g	<a href="#">KCUAB</a>	5055386509505
KCUAB3Bpm	USB3 A female to B female adapter reversible			
KOLADXBpm	Fibre female to female coupler, LC APC to LC APC, single mode duplex	35 x 19 x 35 – 6.5g	<a href="#">KOLADX</a>	5055386509512
KUCC20Bpm	USB C female keystone to C male 20cm tailed lead	200 x 33.67 x 16.30 – 34g	<a href="#">KUCC*20</a>	5055386512918
KOLMMDXBpm	Fibre female to female coupler LC to LC, multi mode duplex	33 x 19 x 35 – 6.5g	<a href="#">KOLMMDX</a>	5055386509529
KOLSMDXBpm	Fibre female to female coupler LC to LC, single mode duplex	34 x 19 x 35 – 6.5g	<a href="#">KOLSMDX</a>	5055386509536
KSH66Bpm	RJ12 6p6c socket	36.4 x 22.8 x 35 – 8.5g	<a href="#">KSH66</a>	5055386509543
KUA2Bpm	USB2 A Screw Termination Socket	28.4 x 19 x 35 – 8.5g	<a href="#">KUA2</a>	5055386509550
SACK3SBpm	Category 6 female to female coupler, shielded	30 x 19 x 35 – 20.5g	<a href="#">SACK3S</a>	5055386509574

SACK4Bpm	Category 6 unshielded compact coupler	30 x 19 x 35 – 8.5g	<a href="#">SACK4</a>	5055386509581
SEKjeBpm	Category 8 socket	41.6 x 19 x 35 – 30.5g	<a href="#">SEKje</a>	5055386509598
SGACK2SBpm	Category 6A female to female coupler, shielded	29.7 x 19 x 35 – 19.5g	<a href="#">SGACK2S</a>	5055386509604
SGACK902SBpm	Category 6A female to female coupler, w/rear outlet 90° to front outlet, shielded (suitable for Cat 6 or Cat 5e)	36.1 x 19 x 35 – 12.5g	<a href="#">SGACK902s</a>	5055386509611
SGACK90Bpm	Category 6A female to female coupler, w/rear outlet 90° to front outlet Unshielded	36.1 x 19 x 35 – 8g	<a href="#">SGACK90</a>	
SGKSjeBpm	Category 6A shielded socket	37.8 x 19 x 35 – 24.5g	<a href="#">SGKSje</a>	5055386509628
SGKSLJBpm	Category 6A STP tool-less locking socket	38.75 x 19 x 35 – 20.5g	<a href="#">SGKSLJ</a>	5055386509840
SGKSbtBpm	Category 6A contractor grade shielded socket	47 x 24 x 18mm – 24g	<a href="#">SGKSbt</a>	5055386512765
SKFBpm	Category 6 tool-less IDC socket, unshielded	38 x 19 x 35 – 10.5g	<a href="#">SKF*</a>	5055386509635
SKmcBpm	Category 6 IDC socket, LSA-Plus and 110 type termination, unshielded	34 x 19 x 35 – 8.5g	<a href="#">SKmc</a>	5055386509642
SLJBpm	LOKJAC Category 6 tool-less locking socket	36 x 19 x 35 – 8.5g	<a href="#">SLJ</a>	5055386509659
SGKctBpm	Category 6A Toolless UTP socket	17 x 19.5 x 37.90 – 10g	<a href="#">SGKctbk</a>	5055386511416
KAPMBfnl	Low profile black panel mount adaptor	11 x 19 x 35 – 2.5g	<a href="#">KAPMBfnl</a>	5055386509420
KAPMBfnl#20	Low profile black panel mount adaptor in bags of 20	25 x 180 x 110 – 100g	<a href="#">KAPMBfnl</a>	5055386509437
KAPMkpk	Low profile black panel mount blank	11 x 19 x 35 – 2.7g	<a href="#">KAPMkpk</a>	5055386509444
KAPMkpk#20	Low profile black panel mount blank in bags of 20	25 x 180 x 110 – 100g	<a href="#">KAPMkpk</a>	5055386509451
KAPMkpk2	Clip-in blank for flexible applications, allows for installation of connectors	20.1 x 19 x 35 – 3g	<a href="#">KPKbk</a>	5055386509697
FFPM16, FFPM16CM	Panel mount 16 port-panel available both with, and without cable management.	482 x 14 x 44.2 – 364g, 482 x 68.4 x 44.2 – 474g	<a href="#">FFPM16</a> , <a href="#">FFPM16CM</a>	5055386508805, 5055386508812

## More Information:

TUK's Low Profile Panel Mount Range offers a wide variety of audio, video and data connectors which can easily be mounted into panels of virtually any thickness.

Each connector is supplied as a kit. Kit includes coupler/connector, panel mount adaptor, and 2 pairs of black steel flat head screws (2 x M3s for European installations, 2 x 4:40s for US installations).

The Low Profile Black adaptor KAPMBfnl is durable and ensures easy mounting (into standard cut-out) – can be purchased on its own in packs of 20 pcs.

All connectors are made to relevant standards. Category 6 and 6A connectors are produced, for example, to FCC68 and to TIA/EIA 568B and have an insertion life of > 750 mating cycles. All products are CE compliant (i.e including ROHS and REACH)

13<sup>th</sup> November 2024

### Rear View



FACK2SBpm



FACK4Bpm



FKFBpm



KBNC1275BPM



KBNC50Bpm



KCF3GBpm



KCHDBpm



KCK66Bpm



KCUAA2Bpm



KCUABBpm



KOLADXBpm



KOLMMDXBpm



FFPM16MC



FFPM16





KOLSMDXBpm



KSH66Bpm



SACK3SBpm



SACK4Bpm



SEKjeBpm



SGACK2SBpm



SGACK902SBpm



SGKSjeBpm



SGKSLJBpm



SKFBpm



SKmcBpm



SLJBpm



SGKctBpm



KAPMBfnl



KAPMkpk



KAPMkpk2

TUK Ltd, Unit 4, Wimbledon Stadium Business Centre, Riverside Road, London SW17 0BA