

PRODUCT-DETAILS

JSTD25H

JSTD25H Two-Hand device



General Information

Extended Product Type	JSTD25H
Product ID	2TLA020007R6300
EAN	7350024460346
Catalog Description	JSTD25H Two-Hand device
Long Description	Two-hand device with JSTD1-B Safeballs. Safeballs are side mounted on a 44x88 extruded aluminum profile designed for two-hand applications. Pre-wired to a M12-8 male connector with protective flanges on the safeballs.

Additional Information

Product Name	Two-Hand device
--------------	-----------------

Safety Information

Performance Level (PL)	Up to e
------------------------	---------

Technical

Connection Configuration	M12-8 male
--------------------------	------------

Popular Downloads

Data Sheet, Technical Information	2TLC010001C0202
Data Sheet, Technical Information (Part 2)	2TLC010069D0201
Instructions and Manuals	2TLC172185M0201

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	2TLC172023D0201
Instructions and Manuals	2TLC172185M0201
SEMKO Certificate	2TLC172034D0201

Dimensions

Product Net Width	370 mm
Product Net Depth / Length	90.5 mm
Product Net Height	130 mm
Product Net Weight	1.167 kg

Ordering

Minimum Order Quantity	1 piece
Country of Origin	Sweden (SE)
Customs Tariff Number	85365011

Classifications

Object Classification Code	B
ETIM 7	EC001260 - Two-hand control device
ETIM 8	EC001260 - Two-hand control device
eClass	V11.0 : 27371219
UNSPSC	32151802

Categories

Low Voltage Products and Systems → Control Products → Safety Products → Safety Control Devices → JSTD25

