



Product data sheet

Power tools for trade & industry

Reciprocating Saw

PRO GSA 18V-24



Compact reciprocating saw for easy cutting even in narrow spaces

The most important data

Battery voltage	18.0 V
Cutting depth in wood	230 mm

Part Number 0 601 6A5 101

Technical data

Technical data

Cutting depth in wood	230 mm
Weight excl. battery	1.7 kg
Battery voltage	18.0 V
Packaging dimensions (width x length x height)	360 x 444 x 151 mm
BITURBO	No
No-load stroke rate	0 - 3100
Stroke length	24 mm

Noise/vibration information

Sawing wood

Vibration emission value ah	9.1 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Makes cutting in narrow spaces easier thanks to compact and ergonomic design
- Makes powerful cuts easier with its outstanding power-to-weight ratio
- Comfortable cutting, thanks to counter-balance mechanism that minimizes vibration



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

