

## SA-11; 0 ... 6 bar; 4...20 mA, 2-W

### Pressure transmitter for sanitary applications

Item number: 43992241

Quantity: 1 pcs.

Order code: SA-11-A-BBH-SJ-AGM4ZZ-ZZZ W101Z-F2B-GSSAK6  
LABEL-PG1DE-ZZZZZ-ZZZZZ

Overview: SA-11; 0 ... 6 bar; 4...20 mA, 2-W  
@ 10 ... 30 V DC; Accuracy: 0.5% of span  
union nut DIN 11851 with conical coupling DN 25;  
circular connector M12x1, 4-pin UB=1, 0V=3  
Specifications according to data sheet: PE 81.80  
System fill fluid: KN 77 Synthetic oil

Label: WIKA standard without / with Tag-number

Details: Pressure transmitter for sanitary applications  
Model SA-11  
Specifications according to data sheet: PE 81.80  
Wetted parts: stainless steel 1.4435  
Case: stainless steel  
Permissible medium temperature: -20 ... +150 °C (-4 ... +302 °F)  
Output signal: 4 ... 20 mA, 2-wire  
Unit: bar  
Measuring range: 0 ... 6 bar  
Process connection: union nut DIN 11851 with conical coupling DN 25  
Accuracy: 0.5% of span  
Electrical connection: circular connector M12x1, 4-pin  
Power supply: 10 ... 30 V DC  
Pin assignment: UB=1, 0V=3  
\*Made in Germany\* on label  
WIKA standard - specification according to data sheet  
System fill fluid: KN 77 Synthetic oil  
Import documentation CIS-States: without

Label: WIKA standard without / with Tag-number