

FEATURES

- Momentary foot switch controller
- SPDT, momentary footswitch with integral non-slip base pad
- Cable and contacts module
- Complete with 2m of cable
- Contact rating 24V ac/dc 3A
- Sealed to IP67 – protected from dust and water

RS PRO General Purpose Momentary Foot Switch - Thermoplastic Case Material, SP-CO, 3 A Contact Current, 24V Contact

RS Stock No.: 774-8614



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO momentary foot switch has been designed with an integral non-slip base pad. It is manufactured from thermoplastic and has Single Pole Double Throw (SPDT) contacts. This foot controller pedal is black and sealed to IP67.

General Specifications

Contact Configuration	SP-CO
Switch Operation	Momentary
Case Material	Thermoplastic
Switch Environment	General Purpose
Contact Material	Silver
Colour	Black
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	Straight 2metre long cable

Electrical Specifications

Contact Voltage Rating (AC)	24V
Contact Voltage Rating (DC)	24V
Contact Current Rating	3A

Mechanical Specifications

Length	96mm
Height	26mm
Dimensions	96mm x 72mm x 26mm
Width	72mm

Protection Category

IP Rating	IPX7
-----------	------

Approvals

Standards Met	ANSI/AAMI ES60601-1:2005/(R)2012, CSA C22.2 No. 60601-1:14, EN 60601-1:2006, EN 60950, UL 60601-1:2005, UL File No E353500
Compliance/Certifications	RoHS



