

FEATURES

- Base material: High Speed Steel
- Straight cylindrical shank
- Right hand cutting
- Rolled spiral flute with ground point, vapour – plated
- Two-cutter, cylindrical, two flutes

RS PRO HSS Twist Drill Bit, 12mm x 315mm

RS Stock No.: 522-6932



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This Metric Extra Length Twist Drill Bit from our own RS PRO brand is an industrial grade drill bit in super high speed HSS steel for accurate and easy drilling of all metals, special and hardened steels and alloys.

General Specifications

Drill Bit Type	Twist Drill Bit
Type	Jobber, Long
Material	HSS
Shank Type	Plain
Cutting Direction	Right Hand
Drilling Application	For Use on Steel & Cast Iron

Mechanical Specifications

Overall Length	315mm
Point Angle	118°
Diameter	12mm

Approvals

Compliance/Certifications	DIN 340, BS 328, RN & ISO
----------------------------------	---------------------------

