


REV	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	REV	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△	1	REVISED	HJ.KIM	HJ,LEE	17.10.13	△					
△						△					

APPLICABLE STANDARD		USB Type-C Cable and Connector Specification Release 1.2 USB Type-C Connector and Cable Assemblies Compliance Document Revision 1.0
RATING	CURRENT	-
	VOLTAGE	-
OPERATING CONDITION		-30℃ ~ +85℃ (INCLUDING TEMP. RISE), 95% RH MAX. (NON-CONDENSING)
STORAGE CONDITION		-10℃ ~ +60℃ (WITH PACKING), 15% ~ 70% RH
APPLICABLE CABLE		OUTER DIAMETER OF CABLE Ø 4.8

Test Description	Test Procedure	Test Requirement	QT	AT
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORING TO DRAWING.	○	○

REMARKS HIROSE will not guarantee the performance on these specifications in case this product will be mated with the others which is not HIROSE's △	DRAFT	DESIGN	CHECK	APPROVAL	RELEASE
	JS.PARK 16.12.07	JS.PARK 16.12.07	HJ.LEE 16.12.07	TS.KANG 16.12.07	

NOTE) QT : QUALIFICATION TEST, AT : ASSURANCE TEST

DWG NO ELC4-632262	CL NO CL 6240-0007-5	PART NO CX60-SLDA
-----------------------	-------------------------	----------------------