

Eaton 12BFGHF90

Catalog Number: 12BFGHF90

Air fuse-link, medium voltage, 90 A, AC 12 kV, 76 x 461 mm, back-up, BS, with striker, style F tags

General specifications



Product Name	Catalog Number
Eaton Bussmann series medium voltage BS air fuse	12BFGHF90
	EAN 5027590432016
Product Length/Depth	Product Height
461 mm	76 mm
Product Width	Product Weight
76 mm	4200 g
Compliances	
BS 2692-1	

Product specifications

Resources

Used with

A3354730 Fuse clip

Type

Fuse

Application

protection of primary side
transformers
used in fuse switch
combination units, fuse
bases and fuse switches

Amperage Rating

90 A

Fuse indicator

With Striker

Fuse size

76 x 461 mm

Breaking capacity

40 kA

Installation technique

Air

Performance Cat According To IEC 60282-1

Back-up

Product application

Primary side transformer protection

Rated frequency - max

50 Hz

Rated frequency - min

50 Hz

Release characteristic

Other

Standard

British Standard

Utilization category

Other

Voltage type

AC

With striker

Yes

Class

Class back-up

Fuse shape

Cylindrical, offset bolted tags

Pre arc (I²T)

8.1 x 103

Resistance

8.37 ohms

Fuse diameter

76 mm

Interrupt rating

40 kAIC

Construction size

76 x 461 mm

Mounting method

Clip-in

Voltage rating

12 kV

Fuse type

BFGH



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia