




Process adapters aseptic flange DIN11864-2A

ADAPT DIN11864-2A DN50



Application		
Design	for volumetric flow meters SMF	
Application	food and beverage industry; hygienic systems	
Pressure rating	25 bar	2.5 MPa
Tests / approvals		
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.	
Safety instructions	The compatibility between medium and product material has to be checked in all applications.	
Mechanical data		
Weight	[g]	3254.4
Materials	stainless steel (316L/1.4404)	
Nominal diameter	DN50 (2")	
Sensor connection	ifm-specific device flange	
Process connection	aseptic flange DIN 11864-2A	
Process connection suitable for pipe standard	(DIN EN 10357 series A); (DIN 11866 series A); (DIN 11850 series 1); (DIN 11850 series 2)	
Surface characteristics Ra/Rz of the wetted parts	Ra ≤ 0.4 µm	



Process adapters aseptic flange DIN11864-2A

ADAPT DIN11864-2A DN50

Accessories	
Items supplied	screws 8
Remarks	
Pack quantity	2 pcs.