



Cut



Light Duty

Ultralight polyurethane gloves combining dexterity and advanced cut protection technology

- **Advanced lightweight design:** HyFlex® 11-518 industrial working gloves' ultralight seamless liner grants users an almost barehanded feel
- **Enhanced defenses:** Dyneema® Diamond Technology fiber provides protection against lacerations, meeting ANSI/ISEA 105-2024 CUT A2 and EN ISO B protection standards
- **Superior durability:** HyFlex® 11-518 PPE gloves offer EN and ANSI/ISEA 105-2024 ABRASION LEVEL 3, ensuring durable personal protection
- **Supreme flexibility:** Their thin, flexible liner also ensures optimal dexterity and tactility in daily use
- **Genuine comfort:** D3 Pinky Knitting technology means the HyFlex® 11-518's form aligns with natural hand contours, for a more tailored fit



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical
- Utilities
- Warehousing

Applications

- Assembly & inspection of components
- Press injection molding
- Picking, fastening components
- Final assembly
- Delivery of parts to production line
- Applying finish to materials, products
- Handling incoming goods

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-518

Ultra light weight cut protection with outstanding dexterity and maximum comfort

Key Features

- **Ultralight seamless liner:** Safety gloves with a barehand feel
- **Dyneema® Diamond Technology:** ANSI/ISEA 1052024 CUT A2 and EN ISO B
- **Durable PU coating:** ANSI/ISEA 105-2024 ABRASION LEVEL 3 resistance

Technologies



Fibre glass free

Performance Standards & Regulatory Compliance



ANSI/ISEA 105-2024



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
HyFlex® 11-518	Finishing: Palm Coated Coating Material: Polyurethane Liner Material: Nylon, Spandex, Dyneema® Diamond Technology Cuff Style: Knitwrist	18	6, 7, 8, 9, 10, 11	210-265 mm; 8.27-10.43 inches	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Ansell