



Needle roller bearings NK80/25-XL (Series NK)

light series

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	80 mm	
D	95 mm	
C	25 mm	
rmin	1 mm	
m	301 g	Mass
Cr	63000 N	Basic dynamic load rating, radial
C0r	119000 N	Basic static load rating, radial
Cur	20000 N	Fatigue limit load, radial
nG	5800 1/min	Limiting speed
n9r	3750 1/min	Reference speed

