



JKL LAMP PART NUMBER	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mA rms)	BRIGHTNESS (CANDELA/m ²)	*RATED LIFE (HRS)
BF26214-20B	5600°k (REF.) x = 0.333 ± 0.01 y = 0.345 ± 0.01	1450 @ 0°C	620	5	30,000 ± 10%	20,000

* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0		 JKL COMPONENTS CORPORATION									
				TITLE MINIATURE COLD CATHODE FLUORESCENT LAMP									
C STRAIGHT ENDS + x & y's B 214±3.0 TO 214±2.0 A DIMENSION CORRECTION-240 TO 214 RELEASED		7/7/03 5/18/01 12/19/00 12/5/00		DRAWN BY L. WENGSTROM		APPV'D BY DATE F.D. 7/7/03		SIZE A		FSCM NO. 55335		DRAWING NO. BF26214-20B	
REV. NO. DESCRIPTION/ECO NUMBER		APPV'D DATE		- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE NONE		RELEASED DATE 12/5/00		REVISION DATE 7/7/03		REV. NO. C SHEET 1 of 1	