

WP-FS IP68 M32 - Flat gasket

3241164

<https://www.phoenixcontact.com/gb/products/3241164>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Flat gasket, material: Perbunan, degree of protection: IP68, color: black, inside diameter: 32 mm



Your advantages

- The Perbunan flat sealing rings are used to seal protective hose screw connections on uneven surfaces.
- Up to IP68 protection is achieved.

Commercial data

Item number	3241164
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	AF7DSA
Product key	AF7DSA
Catalog page	Page 606 (C-3-2019)
GTIN	4046356785709
Weight per piece (including packing)	2.048 g
Weight per piece (excluding packing)	2.354 g
Customs tariff number	40169300
Country of origin	DE

WP-FS IP68 M32 - Flat gasket



3241164

<https://www.phoenixcontact.com/gb/products/3241164>

Technical data

Product properties

Product type	Seal
Thread type	M32

Dimensions

Height	2.2 mm
Diameter	44 mm
Panel thickness	2.2 mm

Internal dimensions

Internal diameter	32 mm
-------------------	-------

Material specifications

Material	Perbunan
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP68
Ambient temperature (operation)	-20 °C ... 120 °C

WP-FS IP68 M32 - Flat gasket



3241164

<https://www.phoenixcontact.com/gb/products/3241164>

Classifications

ECLASS

ECLASS-13.0	27430319
-------------	----------

ETIM

ETIM 9.0	EC001181
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

WP-FS IP68 M32 - Flat gasket

3241164

<https://www.phoenixcontact.com/gb/products/3241164>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk