



### Main

Product name	Cableline 40
Product or component type	Bend
Colour tint	White
Quantity per set	Set of 1

### Complementary

Trunking dimension	145 x 40 mm
Material	UPVC (unplasticized polyvinyl chloride)

### Environment

Ambient air temperature for operation	-5...60 °C
---------------------------------------	------------

### Packing Units

Package 1 Weight	1.000 G
Package 1 Height	1.000 Mm
Package 1 width	1.000 Mm
Package 1 Length	1.000 Mm

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

### Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**