

Features

- Length: 1m
- Power: 240W
- Data rate: 40Gbps
- E-Marker chip
- 1 Right Angled Connector

RS PRO 1m USB4 40Gbps EPR Cable - Right Angled Connector

RS Stock No.: 0839496



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

USB4™ is the most recent update in the evolution of USB. The maximum bandwidth is now 40Gbps, double the previous best spec of 20Gbps (USB3.2 Gen 2x2). It is based on Thunderbolt 3 technology ensuring greater compatibility with all USB Type C and Thunderbolt 3 devices.

This cable supports Extended Power Range at 240W.

General Specifications

USB Type	USB4 40Gbps
Connector A	USB-C
Connector A Gender	Male
Connector A Style	Plug, straight
Connector B	USB-C
Connector B Gender	Male
Connector B Style	Plug, right angled
Data Transfer Rate	40Gbps
Outer Sheath Material	TPE
Sheath Colour	Black
Connector Plating	Nickel
Length	1m
Power	240W EPR

Approvals

Standards Met	CE UKCA ROHS REACH
---------------	--------------------

Similar Products

Stock No.	Brand	Product Name
0839496	RS PRO	1m USB4 40Gbps 240W EPR Cable - R/A Connector
0839501	RS PRO	1m USB4 20Gbps 240W EPR Cable - R/A Connector
0839503	RS PRO	2m USB4 20Gbps 240W EPR Cable - R/A Connector

