

Features

- USB-C Male
- 3.5mm TRS Female
- USB-C Female (PD)

RS PRO USB-C 3.5mm Audio Adapter with Power Delivery

RS Stock No.: 0839462



RS Professionally Approved Products bring to you, professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

With phone manufacturers trying to save space to make phones smaller, they are reducing the number of ports on a phone to just one USB C port. This means that adapters must be purchased to use accessories etc. The USB Type C 3.5mm audio adapter with Power Delivery will allow you to connect 3.5mm stereo equipment to your USB type C (only) phone/tablet. The Power Delivery allows your device to be charged at a quick rate. The 3.5mm socket is used for audio output only.

PLEASE NOTE: This audio adapter will not work with phones/tablets etc that have a 3.5mm port as the phones cannot detect USB C adapter and defaults to speaker.

General Specifications


Connector A	USB-C
Connector A Gender	Male
Connector B	3.5mm TRS
Connector B Gender	Female
Connector C	USB-C (60W Power Delivery)
Connector C Gender	Female
Colour	Silver
Applications	Suitable for smartphones

Approvals

Standards Met	CE UKCA ROHS REACH
---------------	--------------------

Similar Products

Stock No.	Brand	Product Name
0839461	RS PRO	USB-C to 3.5mm audio adapter with PD - Black
0839462	RS PRO	USB-C to 3.5mm audio adapter with PD - Silver
0839465	RS PRO	USB-C to 2.5Gbps Ethernet adapter
USB3C-ETHGHUBA	RS PRO	USB-C to 3x USB3.0 Hub with Gigabit RJ45
0839467	RS PRO	USB-C to HDMI (F) adapter
0839468	RS PRO	USB-C to HDMI adapter with PD
0839488	RS PRO	USB-C to HDMI, USB & Gigabit adapter with PD
0839489	RS PRO	USB-C to HDMI / USB-A x2 /SD / TF with DP1.4 Alt mode
0839490	RS PRO	USB-C to HDMI & USB adapter with PD
0839491	RS PRO	USB-C to HDMI and VGA adapter
0839492	RS PRO	USB-C to HDMI, DVI and VGA
0839493	RS PRO	USB C to Mini DisplayPort adapter



- CONNECTORS: Ø3.5 STEREO JACK*1PCS, TYPE C F*1PCS, TYPE C M*1PCS(SHELL NICKEL).
- MOLD: MOLDING TYPE.
- CONTACTS:
- Test machine test condition.
 - A.100% OPEN, SHORT & INTERMITTANCE TEST.
 - B.CONDUCTOR RESISTANCE: 3ohms MAX:
 - C.INSULATION RESISTANCE: 10MΩ Min/, 10ms: