



NEU
NEW



Product information

Mobile LED Light JARO 7003 CM, 7200lm, 80W, IP65, 110V *GB*

For indoor and outdoor use, IP 65.

- LED Light with extra bright Everlight SMD LEDs.
 - Solid and modern aluminium casing.
 - Stable steel tube frame with plastic corner protectors and ergonomically formed plastic carrier handle.
 - Steplessly pivotable light which can be locked with one hand by means of a quick-release fastener.
 - With safety glass.
 - In colourful display-packaging.
 - This luminaire contains built-in LED lamps.
 - Light unit not replaceable.
- Scope of delivery: 1x JARO 7003 CM LED floodlight with 5m cable and CEE plug - in best brennenstuhl® quality

Technical information

Product number	1171253830
EAN-Code	4007123656165
UP	1
Total luminous flux	7200 lm
Power	80 W
Efficacy	91 lm/W
Energy efficiency class	A+
Nominal input voltage	110 V
Max. nominal input voltage	130 V
Cable length	2 m
Cable designation	H07RN-F 3G1,0
Degree of protection (IP)	IP65
Protection class	I
Colour	black, Yellow
Fittings	Without
Weight of product (without packaging)	4,70 kg
Length of product (without packaging)	40,20 cm
Width of product (without packaging)	20,40 cm
Height of product (without packaging)	34,00 cm

Weight of product (including packaging) 5,27 kg

Length of product (including packaging) 42,00 cm

Width of product (including packaging) 22,00 cm

Height of product (including packaging) 35,00 cm