


Model No.DRT52 CORDLESS TRIMMER



Model No.DRT52 CORDLESS TRIMMER

Item No.	Parts No.	Description	Interchangability	Q'ty	New/Old	Note1	Note2
001	266326-2	TAPPING SCREW 4X18		4			
002	8145G5-1	DRT52 NAME PLATE		1			
003	1830K8-7	HOUSING SET		1			
C10	263005-3	RUBBER PIN 6		2			
D10		INC. 7					
004	620P27-6	SWITCH CIRCUIT		1			
005	141V04-6	SWITCH PLATE COMPLETE		1			
006	8145G6-9	DRT52 SERIAL NO. LABEL		1			
007	1830K8-7	HOUSING SET		1			
C10	263005-3	RUBBER PIN 6		2			
D10		INC. 3					
008	643874-2	TERMINAL		1			
009	620P26-8	CONTROLLER		1			
010	652119-7	PAN HEAD SCREW M2X6		6			
011	629C71-2	STATOR		1			
012	210017-7	BALL BEARING 607DDW		1			
013	519858-1	ROTOR ASSEMBLY		1			
D10		INC. 12,14					
014	211236-8	BALL BEARING 6002DDW		1			
015	267785-3	WAVE WASHER 23		1			
016	141V03-8	OUTER HOUSING COMPLETE		1			
017	266326-2	TAPPING SCREW 4X18		4			
018	763662-2	COLLET CONE 6		1			
019	763661-4	COLLET NUT 6		1			
020	252652-5	THUMB NUT M5		1			
021	941101-4	FLAT WASHER 5		1			
022	226217-9	SPUR GEAR 16		1			
023	265771-8	THUMB SCREW M5X33		1			
024	265763-7	THUMB SCREW M6X25		1			
025	941151-9	FLAT WASHER 6		1			
026	419138-4	BASE		1			
027	410585-2	BASE PROTECTOR		1			
028	265142-9	+ PAN HEAD SCREW M4X10		4			
029	194267-1	TRIMMER BASE ASSEMBLY SET		1			
D10		INC. 20-28					
A01	122703-7	TRIMMER GUIDE ASS'Y		1			
C10	251471-6	- FLAT HEAD SCREW M5		1			
C20	265135-6	+ COUNTERSUNK HEAD SCREW M4X10		1			
C30	265763-7	THUMB SCREW M6X25		1			
C40	265764-5	THUMB SCREW M6		1			
C50	317788-8	GUIDE HOLDER		1			
C60	324378-0	ROLLER 11		1			
C70	341136-9	HOOK		1			
C80	941151-9	FLAT WASHER 6		1			
A02	122704-5	STRAIGHT GUIDE ASS'Y		1			
C10	252649-4	THUMB NUT M6		1			
C20	266339-3	CAP SQUARE NECK BOLT M6X20		1			

C30	343593-7	GUIDE PLATE		1			
A03	191Y83-2	STRAIGHT BIT 6 SET		1			
A04	343577-5	TEMPLET GUIDE 10		1			
A05	781036-5	WRENCH 10		1			
A06	781037-3	WRENCH 17		1			
A07	418647-0	CHIP DEFLECTOR		1			

Please state Parts No. when your order.

Print Date 03/25/2024