2400515

https://www.phoenixcontact.com/gb/products/2400515



Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.



Product Description

The Basicline BL FPM 21.5 is an industrial flat-panel monitor that can be used in applications where a remote display location is required.

Your advantages

- 21.5" display
- DisplayPort 1.2, VGA, and DVI-I input ports
- Integrated configuration buttons
- Ambient operating temperatures from -10 °C ... 60 °C
- 21.5" touch screen display

Commercial Data

Item number	2400515
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	DRBABD
Product Key	DRBABD
Catalog Page	Page 485 (C-6-2019)
GTIN	4055626076201
Weight per Piece (including packing)	7 kg
Weight per Piece (excluding packing)	7 kg
Customs tariff number	85299020
Country of origin	TW

IP65-rated, 21.5-inch, flat panel LCD monitor with projected capacitive touch screen

2400515

https://www.phoenixcontact.com/gb/products/2400515



Technical Data

Product properties

Product type	Monitor
Computer data	
Processor	without
Operating system	without operating system
Cooling	passive
RAM	without RAM
Data storage	without data storage
Slots	without slots
Optical drive	without drive
Display	
Display type	54.6 cm / 21.5"-TFT
Screen resolution	1920 x 1080 Pixel(s) (Full HD)
Touch technology	projective-capacitive, ten-touch control
Display lighting type	LED
Brightness	300 cd/m², typical (adjustable)
MTBF	> 50000 h
Color spectrum	16.7 million colors

Electrical properties

Supply		
Supply voltage	24 V DC (±10 %)	
Power supply unit	24 V DC	
Max. current consumption	0.9 A	

Interfaces

Interfaces	1x USB Type A (For touch control only)
Monitor output	1x DisplayPort
	1x DVI-D
	1x VGA
Network	Without network

Dimensions

External dimensions			
Width / Height / Depth	562 mm / 382 mm / 51 mm		
Installation dimensions			
Width / Height / Installation depth	547 mm / 367 mm /		

Environmental and real-life conditions

2400515

https://www.phoenixcontact.com/gb/products/2400515



Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	-10 °C 60 °C
Ambient temperature (storage/transport)	-20 °C 75 °C
Permissible humidity (operation)	10 % 90 % (non-condensing)
Shock	15g, 11 ms impulse
Vibration (operation)	1g

ounting type	VESA MIS-D, 100
	Front mounting

2400515

https://www.phoenixcontact.com/gb/products/2400515



Approvals			
ERC	EAC Approval ID: RU C-DE.A*08.B01708		
<u>©</u>	UL Listed Approval ID: FILE E 238705		
	CUL Listed Approval ID: FILE E 238705		
EAC	EAC Approval ID: RU D-DE.HB35.B.00389		
-	CGP-SDoC pproval ID: China_RoHS_DRBABD		
c	ULus Listed		

2400515

https://www.phoenixcontact.com/gb/products/2400515



Classifications

ECLASS

ECLASS-10.0.1 19209290 ECLASS-11.0 19200201	ECLASS-9.0	19200403
ECLASS-11.0 19200201	ECLASS-10.0.1	19209290
	ECLASS-11.0	19200201

ETIM

	ETIM 8.0	EC001428			
UN	UNSPSC				
	UNSPSC 21.0	43211900			



2400515 https://www.phoenixcontact.com/gb/products/2400515



Environmental Product Compliance

China RoHS

Environmentally Friendly Use Period = 50 years For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

2400515 https://www.phoenixcontact.com/gb/products/2400515



Accessories

Connecting cable

Connecting cable - VL 2.0M DP CABLE - 2404774 https://www.phoenixcontact.com/gb/products/2404774

DisplayPort (DP) cable (2 m) for use with industrial computers



Mounting flange

Mounting flange - BL FPM MOUNTING KIT - 2403287 https://www.phoenixcontact.com/gb/products/2403287



IPC mounting block style C. Compatible with BL FPM...

2400515 https://www.phoenixcontact.com/gb/products/2400515



Connecting cable

Connecting cable - BL FPM 1.8M DP CBL ACCESSORY - 2404155 https://www.phoenixcontact.com/gb/products/2404155



1.8 m DP to DP cable

Connecting cable

Connecting cable - BL FPM 1.8M DVI CBL ACCESSORY - 2404153 https://www.phoenixcontact.com/gb/products/2404153



1.8 m DVI to DVI cable

2400515 https://www.phoenixcontact.com/gb/products/2400515



PCB connector

PCB connector - MSTB 2,5/ 3-STF - 1786844 https://www.phoenixcontact.com/gb/products/1786844



PCB connector, nominal cross section: 2.5 mm², color: green, nominal current: 12 A, rated voltage (III/2): 320 V, contact surface: Tin, type of contact: Female connector, number of potentials: 3, number of rows: 1, number of positions: 3, number of connections: 3, product range: MSTB 2,5/..-STF, pitch: 5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, locking clip: - without locking clip, plug-in system: COMBICON MSTB 2,5, locking: Screw locking, mounting: Screw flange, type of packaging: packed in cardboard

Phoenix Contact 2022 © - all rights reserved https://www.phoenixcontact.com

PHOENIX CONTACT Ltd Halesfield 13, Telford Shropshire, TF7 4PG 01952 681700 info@phoenixcontact.co.uk