



## Braided Expandable Sleeve – Polyethylene Terephthalate (PET)

- Provides continuous abrasion protection for wires, cables, hoses and tubing
- Highly flexible open weave will not trap heat or humidity
- Allows for use with irregular shapes

- Lightweight, durable protection
- Rated for use up to 257°F (125°C)
- Compliant with U.S. and European passenger rail standards



| Part Number | Color | Nominal I.D. |      | Nominal Diameter Range |             | Length per reel |       | Std. Pkg. Qty. | Std. Ctn. Qty. |
|-------------|-------|--------------|------|------------------------|-------------|-----------------|-------|----------------|----------------|
|             |       | In.          | mm   | In.                    | mm          | Ft.             | m     |                |                |
| SE12P-TR0   | Black | 0.12         | 3.2  | 0.094 – 0.250          | 2.4 – 6.4   | 200             | 61.0  | 1              | 4              |
| SE12P-TR8   | Gray  | 0.12         | 3.2  | 0.094 – 0.250          | 2.4 – 6.4   | 200             | 61.0  | 1              | 4              |
| SE12P-MR0   | Black | 0.12         | 3.2  | 0.094 – 0.250          | 2.4 – 6.4   | 1000            | 304.8 | 1              | 2              |
| SE12P-MR8   | Gray  | 0.12         | 3.2  | 0.094 – 0.250          | 2.4 – 6.4   | 1000            | 304.8 | 1              | 2              |
| SE12P-MR10  | White | 0.12         | 3.2  | 0.094 – 0.250          | 2.4 – 6.4   | 1000            | 304.8 | 1              | 2              |
| SE25P-TR0   | Black | 0.25         | 6.4  | 0.125 – 0.375          | 3.2 – 9.5   | 200             | 61.0  | 1              | 4              |
| SE25P-TR8   | Gray  | 0.25         | 6.4  | 0.125 – 0.375          | 3.2 – 9.5   | 200             | 61.0  | 1              | 4              |
| SE25P-MR0   | Black | 0.25         | 6.4  | 0.125 – 0.375          | 3.2 – 9.5   | 1000            | 304.8 | 1              | 2              |
| SE25P-MR8   | Gray  | 0.25         | 6.4  | 0.125 – 0.375          | 3.2 – 9.5   | 1000            | 304.8 | 1              | 2              |
| SE25P-MR10  | White | 0.25         | 6.4  | 0.125 – 0.375          | 3.2 – 9.5   | 1000            | 304.8 | 1              | 2              |
| SE38P-TR0   | Black | 0.38         | 9.5  | 0.188 – 0.500          | 4.8 – 15.9  | 200             | 61.0  | 1              | 4              |
| SE38P-TR8   | Gray  | 0.38         | 9.5  | 0.188 – 0.500          | 4.8 – 15.9  | 200             | 61.0  | 1              | 4              |
| SE38P-MR0   | Black | 0.38         | 9.5  | 0.188 – 0.500          | 4.8 – 15.9  | 1000            | 304.8 | 1              | 2              |
| SE38P-MR8   | Gray  | 0.38         | 9.5  | 0.188 – 0.500          | 4.8 – 15.9  | 1000            | 304.8 | 1              | 2              |
| SE38P-MR10  | White | 0.38         | 9.5  | 0.188 – 0.500          | 4.8 – 15.9  | 1000            | 304.8 | 1              | 2              |
| SE50P-CR0   | Black | 0.50         | 12.7 | 0.250 – 0.750          | 6.4 – 19.1  | 100             | 30.5  | 1              | 4              |
| SE50P-CR8   | Gray  | 0.50         | 12.7 | 0.250 – 0.750          | 6.4 – 19.1  | 100             | 30.5  | 1              | 4              |
| SE50P-DR0   | Black | 0.50         | 12.7 | 0.250 – 0.750          | 6.4 – 19.1  | 500             | 152.4 | 1              | 2              |
| SE50P-DR8   | Gray  | 0.50         | 12.7 | 0.250 – 0.750          | 6.4 – 19.1  | 500             | 152.4 | 1              | 2              |
| SE50P-DR10  | White | 0.50         | 12.7 | 0.250 – 0.750          | 6.4 – 19.1  | 500             | 152.4 | 1              | 2              |
| SE75P-CR0   | Black | 0.75         | 19.1 | 0.500 – 1.25           | 12.7 – 31.8 | 100             | 30.5  | 1              | 4              |
| SE75P-CR8   | Gray  | 0.75         | 19.1 | 0.500 – 1.25           | 12.7 – 31.8 | 100             | 30.5  | 1              | 4              |
| SE75P-DR0   | Black | 0.75         | 19.1 | 0.500 – 1.25           | 12.7 – 31.8 | 500             | 152.4 | 1              | 2              |
| SE75P-DR8   | Gray  | 0.75         | 19.1 | 0.500 – 1.25           | 12.7 – 31.8 | 500             | 152.4 | 1              | 2              |
| SE75P-DR10  | White | 0.75         | 19.1 | 0.500 – 1.25           | 12.7 – 31.8 | 500             | 152.4 | 1              | 2              |
| SE125P-LR0  | Black | 1.25         | 31.8 | 0.750 – 1.50           | 19.1 – 38.1 | 50              | 15.2  | 1              | 4              |
| SE125P-LR8  | Gray  | 1.25         | 31.8 | 0.750 – 1.50           | 19.1 – 38.1 | 50              | 15.2  | 1              | 4              |
| SE125P-TR0  | Black | 1.25         | 31.8 | 0.750 – 1.50           | 19.1 – 38.1 | 200             | 61.0  | 1              | 2              |
| SE125P-TR8  | Gray  | 1.25         | 31.8 | 0.750 – 1.50           | 19.1 – 38.1 | 200             | 61.0  | 1              | 2              |
| SE125P-TR10 | White | 1.25         | 31.8 | 0.750 – 1.50           | 19.1 – 38.1 | 200             | 61.0  | 1              | 2              |
| SE150P-LR0  | Black | 1.50         | 38.1 | 1.00 – 2.13            | 25.4 – 57.2 | 50              | 15.2  | 1              | 4              |
| SE150P-LR8  | Gray  | 1.50         | 38.1 | 1.00 – 2.13            | 25.4 – 57.2 | 50              | 15.2  | 1              | 4              |
| SE150P-TR0  | Black | 1.50         | 38.1 | 1.00 – 2.13            | 25.4 – 57.2 | 200             | 61.0  | 1              | 2              |
| SE150P-TR8  | Gray  | 1.50         | 38.1 | 1.00 – 2.13            | 25.4 – 57.2 | 200             | 61.0  | 1              | 2              |
| SE150P-TR10 | White | 1.50         | 38.1 | 1.00 – 2.13            | 25.4 – 57.2 | 200             | 61.0  | 1              | 2              |
| SE175P-TR0  | Black | 1.75         | 44.5 | 1.25 – 2.75            | 31.8 – 69.9 | 200             | 61.0  | 1              | 2              |

Reel packaging may contain splices. Contact Panduit Customer Service for further information.

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index