



THE POWER TO PRINT

Available from:

Ap1310 Thermal Portable Printer – with 38m long paper roll & label or Bluetooth options

Head Office

(Production, Sales, Design and Repair)

ABLE Systems Limited
Denton Drive
NORTHWICH
Cheshire
CW9 7TU
England

Tel: +44 (0) 1606 48621
Fax: +44 (0) 1606 44903

E-mail:
contact@able-systems.com



Compact and stylish

- Unique SINGLE-handed easy paper-load system – no other printer is easier!
- Utilising a high speed and high quality fixed head thermal mechanism with superb quality text.
- Capable of printing on linerless labels.
- Choice of interface solutions including Serial RS232, full implementation IrDA and Bluetooth.
- Strong case design that won't stress the lid hinge.
- Miniature size - yet takes up to 38m long paper roll.
- Choice of battery management within one printer (re-chargeable within the unit or use primary cells). In-vehicle solutions and mains supply also available.



Design registered.

Typical Applications include:

Mobile ticketing and recording. Use with PDA's. Labelling. Queue busting. Utility billing. In-vehicle receipting. Financial transactions. Taxi receipt printing. Law enforcement agencies. Test and measurement. Medical. Hospitality. Restaurants.

www.powertoprint.com

Ap1310 Thermal Portable Printer – with 38m long paper roll & label or Bluetooth options

Specification	Ap1310	Ap1310-IR	Ap1310-BT
Data Input	RS-232 Serial (RJ12 connector)	RS-232 Serial (RJ12 connector)	RS-232 Serial (RJ12 connector)
Wireless Data Input	N/A	IrDA (IrPHY V1.0, IrLAP, IrLMP, IAS, TinyTP, IrCOMM 9-wire)	Bluetooth
Print Method	Fujitsu fixed head thermal mechanism		
Print Speed	60 mm/s (at 7.2V battery voltage); 50mm/s (typical)		
Paper Specification	Paper Roll Width: 57.5 ± 0.5mm. Max roll diameter: 55mm (Length: 37.7m @ 60um thickness) Accepts paper rolls with or without a core		
Print Width	48 mm		
Dots per line (graphics)	384		
Dot spacing	8 dots/mm (vertical and horizontal)		
Sensors	Paper Out (Opto reflective) and Head Up (Mechanical)		
Data Buffer	20 Kb		
Baud Rate	Up to 57,600 (9600 Default)		
Character Set	IBM® 224 character set, CP437. (See note 1)		
Number of columns	12, 16, 21, 24, 42, 32 (Default). (See note 1)		
Font (dots)	7 x 24, 10 x 24 (Default). (See note 1)		
Dimensions	65 x 95 x 128 mm (H x W x L)		
Weight	446g (including battery and full roll of paper)		
Power Supply Options	As standard the Ap1310 range is supplied with a shrink-wrapped re-chargeable battery pack (5 cell 6V NiMH), together with an adapter to allow the use of primary cells. Note that chargers and data or power cables need to be ordered separately (see below) or as part of a complete kit. Power supply options include: <ul style="list-style-type: none"> BC1300V2: Universal i/p trickle charger BC1300FC: Universal i/p combined fast charger and 12V vehicle charger 		
Other options	<ul style="list-style-type: none"> Ap1300BR-01: Combined wall mounting bracket and belt clip Ap1300-D9: D9 to RJ12 data cable (with jack socket for alternative charging) Ap1300BP-01: Spare NiMH battery pack 		
Windows® Driver	Win98, WinME, WinNT, Win2k, WinXP, Vista and 7 (32 bit).. Download from www.able-systems.com		
Temperature Range (operating)	0 - 50°C		
Reliability - MCBF	10 ⁸ print pulses or 50kms. >13 million print lines (Approx. 3,500 paper rolls).		

Note 1: The proprietary Font Editor Utility software (order code Ap800FEU) enables customisation of character fonts by the user.

Please note that for low volume purchases the Ap1310 family of printers are only available in kit form.

Ap1310-KIT1: comprising an Ap1300 printer fitted with re-chargeable batteries, a BC1300V2 universal trickle charger, an Ap1300-D9 data cable, an Ap1300BR-01 belt clip/wall bracket, an A05836TPR1 paper roll and a primary cell cradle.

Ap1310-IR-KIT1: comprising an Ap1300-IR printer fitted with re-chargeable batteries, a BC1300V2 universal trickle charger, an Ap1300-D9 data cable, an Ap1300BR-01 belt clip/wall bracket, an A05836TPR1 paper roll and a primary cell cradle.

Ap1310-BT-KIT1: comprising an Ap1300-BT printer fitted with re-chargeable batteries, a BC1300V2 universal trickle charger, an Ap1300-D9 data cable, an Ap1300BR-01 belt clip/wall bracket, an A05836TPR1 paper roll and a primary cell cradle.

There are also some **other options** available:

Ap1310-DP as per the standard Ap1310 but suitable for use with mains power (no batteries).

Ap1310-DC as per the standard Ap1310 but with an integral DC:DC converter for automotive applications.

Now available with in-car trickle chargers!

BC1300CLAH – for use with Ap1300BT only.

BC1300CLAL – for use with non Bluetooth printers only.

Other products available from Able Systems include:



Portable printers



Panel mounting printers



Kiosk printers



In-vehicle printers



Printer mechanisms & interfaces



Accessories



Consumables