



Type		IP65 handles for external front-mounted operators			
Switch rating		32...63 A	100...400 A	630...800 A	1250 A
References	Black/grey	GS2AH510 (1)	GS2AH530 (1)	GS2AH550	GS2AH570
	Red/yellow	GS2AH520 (1)	GS2AH540 (1)	GS2AH560	GS2AH580

(1) For external front operators with Test facility, insert the letter T in the reference. Example: GS2AH510 becomes GS2AHT510

Type		IP65 handles for external RH side-mounted operators (2)		
Switch rating		32...63 A	100...400 A	630...1250 A
References	Black/grey	GS2AH210	GS2AH230	GS2AH250
	Red/yellow	GS2AH220	GS2AH240	GS2AH260

(2) For external LH side-mounted operators, replace the number 2 in the reference by 3. Example: GS2AH210 becomes GS2AH310

Type			Shafts for external operators		
Switch rating			32 A	50...400 A	630...1250 A
References	Length of shaft	200 mm	GS2AE82	GS2AE22	GS2AE52
		320 mm	GS2AE8	GS2AE2	GS2AE5
		400 mm	GS2AE81	GS2AE21	GS2AE51

5



Type		Handles for direct operators				
Switch rating		32 A	50 and 63 A	100...400 A	630 and 800 A	1250 A
Type of operator		Front	RH side	RH side	Front	Front
References		GS1AH103	GS1AH01	GS1AH02	GS2AH104	GS2AH105