



ENGLISH

Datasheet

Stock No: 190-838

RS Pro Stainless Steel Threaded Steel & Stainless Steel Pipe



Product Details

Stainless Steel Pipe Schedule 40 150lb Class

A range of welded and seamless stainless steel pipe to ASTM A312 type 316L with BSP taper threads. Supplied in two metre lengths, each tube is threaded at both ends to fit directly on to the range of BSP stainless steel fittings.

Seamless pipe variants are stock nos. 183-7904, 183-7910.

Note

Stainless steel pipe maximum working pressure is 150 PSI at 20°C; maximum working temperature is 600°C. If the pipe is used at above 20°C the pressure must be de-rated by 150//580 psi per 1 °C.

Pipe & Threaded Fittings - Stainless Steel 150lb class



ENGLISH

Specifications:

Material	Stainless Steel
Finish	Stainless Steel
Wall Thickness	0.48mm
Length	2000mm
Connection	1/2 in BSPT
Thread Size	1/2in
Thread Standard	BSPT