

COAST

XP11R PURE BEAM FOCUSING TORCH



DUAL POWER

ZITHION-X™ Rechargeable — Also works with Alkaline batteries



2000
LUMENS OUTPUT

40
HOUR RUNTIME

DUST RESISTANT
IP54

WEATHER PROOF

POWER SOURCE:
LITHIUM OR ALKALINE
3 x AAA

COAST TRUSTED TOUGH™

FIVE YEAR WARRANTY

XP11R



This Workhorse Torch Brings 2000 Lumens on Turbo Mode in COAST's NEW Durable "Extreme Performance" Line of Portable Lighting Solutions

The XP11R brings a new mode to COAST handhelds – Turbo Mode – which will provide 2000 lumens featuring COAST's famously consistent beam. Turbo mode can be accessed with a long push of the rear switch, along with three other modes (low, medium, and high).

The COAST XP11R torch delivers brightest-in-class light, multi-beam capability powered by a COAST ZITHION-X™ rechargeable battery, which can be charged in the torch via a Pro-Tek port or outside of the torch. The torch also features COAST's Dual Power™ technology, meaning it's also compatible with three AAA alkaline batteries (sold separately).

This workhorse features a real-time power indicator plus patented slide-focusing optical technology that shines clean flood light and piercing spot light with seamless transitions between.

- 2000 lumens on Turbo Mode, and 1000 lumens on High
- Length: 6.02 in. / 15.30 cm
- ZITHION-X™ rechargeable battery (included), or 3 x AAA batteries (sold separately)

