



Telephone Cordless

Telephone KX-TGB210

General	Colour	B[Black]
	Colour	W[White]
	Colour	C[Blue]
	Handset (Quantity)	1
	Frequency	1.9 GHz
	Frequency Range	1.88 GHz - 1.90 GHz
	Number of Channels	120 Channels
	System	DECT
	DECT Security Mode	-
	GAP	-
	Number of Phone Lines	1.0
	Multiple Handsets Capability	-
	Multiple Base Units Capability	-
	LCD Language	Dutch, English, French, German, Greek, Italian, Portuguese, Spanish, Turkish
	Wi-Fi® Connection	-
	Mobile Connection	-
	Android™ OS Version	-
Power Saving	Low Radio Power	Y
	One Touch Eco Mode	-
Smartphone Connect	Smartphone Connect	-
	Multiple Smartphones Capability	-
	Supported Devices	-

	Wireless Network Standard	-
	Simplified Configuration	-
	Easy Wi-Fi Setup Button	-
	Wi-Fi Repeater Mode	-
	Phonebook Copy from Smartphone	-
	Ringtone Copy from Smartphone	-
	Wallpaper Image Copy from Smartphone	-
	Conference Call with Outside Landline and Smartphone	-
	Transferring Landline Call (between Smartphone and Handsets)	-
	Playing Answering System Messages	-
Link-to-Mobile	Link-to-Cell	-
	Mobile Registration Number	-
	Simultaneous Communication	-
	Ring as Cell Mode	-
	Text Message Alert	-
	Talking Text Sender Alert	-
	Device Battery Charging	-
Smartphone Docking Station	Smartphone Stand	-
	Stereo Speaker	-
	Compatible Devices of Battery Charging	-
	Playing Music from a Bluetooth Device	-
	Music Player Remote Control by DECT Handset	-
Convenience	Key Finder Compatible	-

Multiple Key Finder Capability	-
Repeater Available	-
Clear Sound	-
Noise Reduction	-
Customized Sound System (Equalizer)	-
Compatible with Hearing Aid T-Coil (TIA-1083 Compliant)	-
Power Back-Up Operation	-
Baby Monitor	-
Smart Function Key	-
Any Key Answer	Y
Do Not Disturb Mode	-
Bypassing Do Not Disturb Mode (Specified Phonebook Category)	-
SMS	-
Voice Mail	-
Voice Mail Alert (Light-Up Indicator on Handset)	-
Call Restriction	-
Distress Call	-
Conference Call with Outside Line	-
Call Share	-
Intercom (Handset to Base Unit)	-
Intercom (Handset to Handset)	-
Intercom All	-
Clock	Y
Calendar/Scheduler	-
Alarm (Wake-up / Memo alarm)	Y/-

	Advanced Alarm (A day of the week / Snooze)	-/Y
	Bluetooth® Headset Capability (HSP Support)	-
	Bluetooth Audio Headphone/Speaker Capability (A2DP Support)	-
	Google Play™ Support	-
Caller ID/ Phonebook	Caller ID	Y
	Caller ID	* Requires subscription to Caller ID service offered by your provider/telephone company.
	Caller ID Memory	50 items
	Caller ID Memory	* Requires subscription to Caller ID service offered by your provider/telephone company.
	Call Waiting Caller ID	Y
	Call Waiting Caller ID	* Requires subscription to both Caller ID and Call Waiting with Caller ID services offered by your provider/telephone company.
	Category Ringer / Ringer ID	-
	Category Display Colours	-
	Talking Caller ID (Handset)	-
	Talking Caller ID (Base Unit)	-
	Talking Caller ID Language	-
	Nuisance Call Block	-
	Block Range of Numbers	-
	Block Withheld Number Call	-
	Handset Phonebook Memory (Name/Number)	50 items
	Handset Phonebook Memory (Name/Number)	(12char/24digits)
	Base Unit Phonebook Memory (Name/Number)	-

	Shared Phonebook	-
	Phonebook Copy (Handset to Handset)	-
	Phonebook Copy from Mobile Phone via Bluetooth	-
	Speed Dial (Handset)	-
	Speed Dial (Base Unit)	-
	Chain Dial	Y(Handset)
Handset	LCD	1.4 inch (3.5 cm)
	LCD	Monochrome
	LCD	12digits x 1line
	LCD	+ Pict x 2lines
	LCD Backlight Colour	Amber
	Touchscreen	-
	Front Camera	-
	Rear Camera	-
	LED Flash	-
	GPS	-
	SD Memory Card Slot	-
	USB Jack	-
	USB Version	-
	Illuminated Keypad	-
	Speakerphone (Volume Steps)	-
	Icon Operation (Number of Icons)	-
	Ringer Pattern (Tone+Melody)	12(6+6)
	Polyphonic Ringer Melody	-
	Ringer Volume Steps	5+OFF

	Receiver Volume Steps	5.0
	Redial Memory	10(Name & Number)
	Redial Memory	* Requires registration in the phonebook to display the name.
	Digits of Redial Number	24.0
	Auto Redial	-
	Ringer Indicator (Colour)	-
	Charge Indicator (Colour)	-
	Hold	-
	Mute	Y
	Recall/Flash	Y
	Key Lock	-
	Headset Jack	-
	Reversible Handset Charging	-
	Secure Grip	-
	Short Stroke Key	-
	Wall Mountable (Charger)	-
Base Unit	Dial Keypad	-
	Corded Handset (Power Outage Operation)	-
	Display	-
	Speakerphone (Volume Steps)	-
	Ringer Pattern (Tone+Melody)	-
	Ringer Volume Steps	-
	Redial Memory	-
	Auto Redial	-
	Mobile Locator	-

	Hold	-
	Mute	-
	Recall/Flash	-
	Handset Locator	Y
	Wall Mountable	-
Answering System	Answering System	-
	Total Recording Time	-
	Fast-Forwarding and Rewinding Message	-
	Audible Message Alert	-
	Message Alert (Light-Up Indicator on Handset)	-
	New Message Notification by a Call	-
	Announcement Language of New Message Notification	-
	New Message Notification by an SMS	-
	Visual Message List (Handset LCD)	-
	Recording Conversation	-
	Speaker Volume Steps(Base Unit Speaker)	-
	Call Screening (Handset)	-
	Call Screening (Base Unit)	-
	Language of Pre-recorded Greeting Message	-
	Remote Operation from Handset	-
	Remote Operation from Outside (DTMF)	-
	Toll Saver (New Messages Recorded / No New Message)	-
Accessories	Key Finder Included (Quantity)	-

	Repeater Included	-
	Belt Clip Included	-
Optional Handset	Optional Handset	-
Others	Radiation Free (Eco Mode Plus)	-
	Rechargeable Battery	Ni-MH(AAA x 2)
	Talk Time	Up to 16 hours
	Standby Time	Up to 280 hours
	Charge Time	About 7 hours
Power Consumption	Base Unit Standby Power Consumption	0.6 W
	Charger Standby Power Consumption	-
Dimensions/ Weight	Base Unit Dimensions (W x D x H)	Approx. 99 mm x 99 mm x 50 mm
	Handset Dimensions (W x D x H)	Approx. 47 mm x 30 mm x 162 mm
	Charger Dimensions (W x D x H)	-
	Key Finder Dimensions (W x D x H)	-
	Repeater Dimensions (W x D x H)	-
	Base Unit Weight	Approx. 80 g
	Handset Weight with Battery	Approx. 130 g
	Charger Weight	-
	Key Finder Weight	-
	Repeater Weight	-