Enclosed Metal Clad Enclosed Isolator



Features

- 4 Pole
- 32A
- IP65 rated
- Enhanced safety
- Easy installation
- Robust & durable
- Wide product range

RS PRO Metal Clad Enclosed Isolator

RS Stock No.: 136-5286





RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Enclosed Metal Clad Enclosed Isolator



Product Description

IP65, RAL 7035, AC-22 Switch Rating.

External mounting brackets, padlockable in the OFF position for added security.

Epoxy powder coated steel, , H:173 x W:100 x D:120mm.

General Specifications

Data		Range	Units	136-5286
Rated Operational Voltage Ue				
IEC & EN		Volts	V	690
UL		Volts	V	600
Main switch Isolating Voltage up to		Volts	V	750
Rated impulse withstand voltage Uimp		Volts	kV	6
Rated uninterrupted current lu		Amps	А	32
Rated Operational Current le				
IEC & EN	AC-22A	Up to 690V	А	32
	AC-21A	Up to 690V	А	40
	AC-1	Up to 690V	А	40
Rated Operational Power AC-23A (50-60Hz)				
IEC & EN	3 Phase	230 (240V)	kW	15
		400 (415)V	kW	18.5
		690V	kW	22
Rated Operational Power AC-3 (50-60Hz)				
IEC & EN	3 Phase	230 (240)V	kW	11
		400 (415)V	kW	11
		690V	kW	15
UL Power Rating				
DOL	3 Phase	120V	hp	3
		240V	hp	7.5
		480V	hp	20
		600V	hp	25
	1 Phase	120V	hp	2
		240V	hp	3
UL Short Circuit Ratings				
Fuse rating, class J		Amps	А	45
Rated Fused short circuit current		Amps	kA	10
Short Circuit Capacity (IEC)				
Max fuse size (Type gl)		Amps	А	32
Rated Fused short circuit current		Amps	kA	30
Terminal Specification				
Single/ Multiple strand wire		Min-mm ²		2.5
		Max-mm²		10
Fine strand with sleeve		Min-mm ²		0.75
		Max-mm²		6
Recommended Tightening Torque	Nm		1.7	

Enclosed Metal Clad Enclosed Isolator



Technical Diagram





