



LASER-TRUMMY2 [↗](#)

Belt tension gauge

System for measuring belt tension

Technical information

Technical data

	10 Hz – 800 Hz	Measuring range frequency
	> 150 mm	Minimum free belt strand
	< 1%	Digital sampling error
	± 1 Hz	Display error
	< 5%	Total error
	+10 °C ... +50 °C	Operating temperature
	Plastic (ABS)	Housing material
	2 lines LCD, 16 characters	Display
	10	Available languages
	≤ 9,99 m	Input limit free strand length
	≤ 9,999 kg/m	Input limit belt mass
	Battery (9 V)	Power supply
	max. 2 years (periodic)	Calibration (recommended)
	80 x 126 x 37	Dimensions device (mm)
	255 x 210 x 60	Dimensions Case (mm)
≈m	0,98 kg	Weight

Additional information

- 1 pc. measuring instrument,
- 1 pc. measurement sensor with c
- 1 pc. plug-in sensor,
- 1 pc. battery,
- 1 pc. transport case
- Included in delivery