

Features

- Grey panel mount sounder
- Intermittent alarm
- Temperature -30°C to +50°C
- IP55 Rated
- 12mm Panel mount fixing
- ABS plastic offering protection against UV and is Impact resistant

RS PRO PANEL MOUNT PIEZO SOUNDER 24VAC/DC

RS Stock No.: 0726247



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Introducing industrial panel mount sounder from RS PRO, a high-quality sounder with Intermittent Alarm. Suitable for 12mm panel mounting, supplied with gland and locking nut for easy installation. Ideal for use in a wide range of control panel, security and process control applications. This durable Sounder is available in grey with an operating voltage of 24V AC DC. The units are supplied fully assembled to enable quick and easy installation via a 12mm hole and secured using the supplied locking ring. This RS PRO sounder is suitable for light and heavy industrial signalling applications, producing an Intermittent alarm to signal hazards and emergencies.

General Specifications

Material	ABS
Sound output	Intermittent sound 82dB(A)1m 4000+/-300Hz
Multi tone	No
Fitting	12mm through hole panel mount
Housing colour	Grey
Lamp included	No
Special features	Gland and locking ring supplied

Electrical Specifications

Supply Voltage	24VAC/DC
Current Type	AC/DC
Current Consumption	7mA

Mechanical Specifications

Dimensions	40 (d) x 62.5mm (h)
Base Diameter	40mm
Mounting Style	Through hole panel mount
Weight	0.04kg

Operation Environment Specifications

Maximum Temperature	-30°C
Minimum Temperature	+50°C

Protection Category

IP Rating	IP55
-----------	------

Approvals

Compliance/Certifications	CE / CSA / UL94-V0
Standards Met	EMC (ECE R10), RoHS Compliant