


REV.	DESCRIPTION/ECO NO.	DATE
	RELEASE	1/27/14



4 PIN JOINER CONNECTOR
 WIRE TYPE: UL1007, 22 AWG

NOTES:

1. OPERATION
1. GENTLY LIFT LATCH AT SIDE OF CONNECTOR.
2. SWING COVER OFF OF CONTACTS.
3. SLIDE THE FLEX TAPE INTO THE CONNECTOR PLACING THE EDGE OF THE FLEX TAPE UNDER THE CONNECTOR COVER.
4. FOLD OVER THE COVER AND PRESS IN PLACE UNTIL THE LATCH IS FULLY ENGAGED.
2. LIMIT CURRENT TO A MAXIMUM OF 5 AMPS.

JKL PART NO.: ZCH-170-RGB-J

USED WITH JKL RGB LED FLEX LIGHT RIBBON
 PART NO.: ZFS-10504-RGB

METRIC		DIMENSIONS ARE IN mm (INCHES)		TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE	
THIRD ANGLE PROJECTION		1 PL +/- REF.		2 PL +/- REF.		JKL COMPONENTS CORPORATION	
DRAWN BY L. WENGSTROM		APP'VD BY		DATE		RGB FLEX RIBBON JOINER CONNECTOR HARNESS	
- CAD DRAWING -		SCALE		SIZE		FSCM NO.	
MANUAL REVISIONS NOT PERMITTED		NONE		A		55335	
		DATE		1/27/14		DRAWING NO.	
						ZCH-170-RGB-J	
		RELEASED DATE		1/27/14		REVISION DATE	
		REV. NO.				SHEET	
		1				1 OF 1	