



Disposable

SOLO 987

Nitrile | Chlorinated

Excellent mechanical resistance, ideal in oily environments

SPECIFIC ADVANTAGES



Comfort

- Excellent dexterity thanks to reduced material thickness



Skin protection

- Recommended for people sensitive to the proteins in natural latex



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Practical

- Easy to put on and take off

INDUSTRIES

- Automotive/mechanical industry
- Laboratory
- Aeronautics industry

APPLICATIONS

- Work with composite materials (resins)
- Manufacturing of medicines
- Pharmaceutical preparation
- Research, analysis, handling of precision parts
- Assembly of small oily parts



CHEMICAL PROTECTION
TYPE B

EN ISO 374-1



TYPE B
JKT

EN ISO 374-5



VIRUS

CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5



Disposable

SOLO 987

Nitrile | Chlorinated

LEGENDS

EN ISO 374-1

CHEMICAL RISKS



TYPE B

J: n-Heptane
K: Sodium hydroxide 40%
T: Formaldehyde 37%

EN ISO 374-5

MICRO-ORGANISMS



VIRUS

Protection against bacteria, fungi and virus

PRODUCT DETAILS

Interior finish	Chlorinated
Exterior finish	Smooth with pebbled fingertips
Material	Nitrile
Colour.s	White
Length (cm)	25
Thickness (mm)	0.1
European sizes	6 7 8 9
AQL Liquidproofness	1.5
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	1.3E+11 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	1.9E+8 Ω

LOGISTIC DETAILS

Packaging

100 gloves/box
1000 gloves/carton

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/02/24/0270 EXT 01/02/24
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France