

FEATURES

- Vinyl coated high tensile steel
- Fits all padlock shackle sizes up to 9mm diameter
- Lock out power switches during maintenance
- Interlocking tabs for additional security
- Compact for easy carrying and storage

6 Lock Steel Hasp Lockout, 38mm Attachment Point

RS Stock No.: 805-5500



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

These Lockout Hasps from our own RS PRO brand are designed with locking clamp which offers a superior strength. They are ideal for lockout applications where more than one safety padlock has to be attached.

General Specifications

Туре	Hasp Lockout	
Material	Steel	
Number of Locks	6	
Colour	Red/ yellow	

Mechanical Specifications

Attachment Point Minimum Size	9mm
Attachment Point Maximum Size	38cm
Lock Shackle Maximum Diameter	9mm

Approvals

Compliance/Certifications ANSI/ESD S20.20:2014 and BS EN 61340-5-1:	2007
---	------





	Total Height	Total Width	Total Depth	Inner Diameter Claw	Inner Diameter Claw	Min. Diameter of hole for hasp
801	118mm	45mm	12mm	1"	25mm	12mm
802	131mm	60mm	12mm	1.5"	40mm	12mm