





Busbar system, accessories Busbar center-to-center spacing 40 mm  
Busbar holder 5-pole 12x 5, 15x 5 as end and intermediate holder



Model	
Product brand name	SENTRON
Operating voltage / at AC / rated value	690 V
Type of connectable conductor cross-sections / for copper conductor / stranded	12 mm - 15 mm x 5 mm
Mechanical Design	
Busbar center-to-center spacing	40 mm
Certificates	

General Product Approval			Declaration of Conformity	Test Certificates	
 CSA	 UR		 EG-Konf.	<a href="#">Special Test Certificate</a>	<a href="#">Miscellaneous</a>

Shipping Approval	other
 PRS	 RINA
	<a href="#">Miscellaneous</a>

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8US1903-5AA00>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/8US1903-5AA00>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8US1903-5AA00](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8US1903-5AA00)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

