

FEATURES

- General-purpose swivel castor
- Light duty
- Load capacity of 70kg
- Wheel diameter of 75mm
- Overall height of 95mm
- Wheel width of 25mm
- Fixing plate dimensions of 75mm x 60mm
- Fixing centres of 55mm x 42mm
- Brakes not included
- Rubber tyres
- Included top plate fitting
- Four fixing holes of 8mm
- Fixed rotation
- Plain bore hub bearings

RS PRO Fixed Castor Wheel, 70kg Load Capacity, 75mm Wheel Diameter

RS Stock No.: 828-6300



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

This 75 mm general-purpose swivel castor is ideal for safely transporting light-duty equipment, whether you're moving appliances across the office or setting up a mobile desk or chair. It can bear loads of up to 70 kg and rotates a full 360° for maximum mobility.

You can fasten this castor to your equipment in a very straightforward manner thanks to its simple rectangular plate mount. Moreover, its polypropylene (PP) hub and pressed steel bracket make it durable, whether you're applying it indoors or on softer outdoor surfaces. Finally, its tyres are conveniently crafted from rubber to protect flooring against marks.

General Specifications

Rotation	Fixed
Weight Class	Light Duty
Load Capacity	70kg
Tyre Material	Rubber
Hub Material	Polypropylene
Bracket Material	Pressed steel
Includes Brake	No
Features	Top Plate Fitting
Applications	General Purpose, offices, warehouses and other industrial environments

Mechanical Specifications

Mounting Type	Plate
Wheel Diameter	75mm
Wheel / Tread Width	25mm
Overall Height	95mm
Number of Fixing Holes	4
Fixing Hole Size	8mm
Hub Bearing Type	Plain Bore



Fixing Centres Specifications	
Fixing Centres	55mm x 42mm
Fixing Centres (Length)	55mm
Fixing Centres (Width)	42mm

Fixing Plate Specifications	
Fixing Plate Dimensions	75mm x 60mm
Fixing Plate Length	75mm
Fixing Plate Width	60mm





Castor Wheels



Application Features Fixing Centres Fixing Centres Length Fixing Centres Width	General Purpose / Industrial Non-Marking 55x42mm 55mm
Fixing Centres Fixing Centres Length	55x42mm
Fixing Centres Length	
	55mm
Fiving Centres Width	
Fixing Centres Width	42mm
Fixing Hole Size	8mm
Fixing Plate Dimensions	75x60mm
Fixing Plate Length	75mm
Fixing Plate Width	60mm
Hub Bearing Type	Plain
Hub Material	Polypropylene
Load Capacity	70kg
Number of Fixing Holes	4
Overall Height	95mm
Rotation	Fixed
Tyre Material	Grey Rubber Tyre
Weight Class	Light Duty
Wheel Diameter	75mm
Wheel Width	