

RSL.151-EP100PB – ¼ & ½ Socket Set 100PC

Description:

- ¼" and ½" Twin box socket set
- Open the box fills one 3-module drawer



Content;

1 x RL.151 ¼" Slim pear head ratchet
1 x R.209ST ¼" 55mm Extension
1 x R.210ST ¼" 100mm Extension
1 x R.240AT ¼" Universal joint
1 x R.236BT ¼" Socket nut handle
1 x R.120AT ¼" Sliding bar handle
12 x R.HT ¼" 6-Point metric sockets – 4 - 5 - 5.5 - 6 - 7 - 8 - 9 - 10 - 11 - 12 - 13 - 14 mm
7 x R.LAT ¼" 6-Point metric deep sockets - 6 - 7 - 8 - 10 - 11 - 12 - 13 - 14 mm
7 x RX.T ¼" TORX® bit sockets – T8 - T10 - T15 - T20 - T25 - T27 - T30 - T40
4 x RT.T ¼" Hex bit sockets – 3 - 4 - 5 - 6 mm
2 x RS.T ¼" Slotted bit sockets – 4 - 7 mm
2 x RD.T ¼" POZIDRIV® bit sockets – PZ1 - PZ2
2 x RP.T ¼" PHILLIPS® bit sockets – PH1 - PH2

1 x SL.151 ½" Slim pear head ratchet
1 x S.210ST ½" 130mm Extension
1 x S.215ST ½" 210mm Extension
1 x S.240AT ½" Universal joint
1 x S.236BT ½" to 5/16" adaptor
1 x J.235TW ¾" to ½" 3-way coupler
17 x S.HT ½" 6-Point metric sockets – 10 - 11 - 12 - 13 - 14 - 15 - 16 - 17 - 18 - 19 - 20 - 21 - 22 - 24 - 27 - 30 - 32 mm
6 x S.LAT ½" 6-Point metric deep sockets – 13 - 14 - 15 - 16 - 17 - 18 - 19 - 22 mm
2 x ½" Spark plug socket – B.S16A1T 16mm - B.S21A2T 21mm
18 x Bits – XZN M6 M8 M10 M12 - PHILLIPS® PH3 PH4 - Slotted 8mm 12mm - Hex 8mm 10mm 12mm 14mm - POZIDRIV® PZ3 PZ4 - TORX® T40 T45 T50 T55