
PANEL LED 1200 40 W 4000 K

LEDVANCE PANEL LED 1200x300 | LED panel luminaires



Areas of application

- Corridors
- Offices
- Conference rooms
- Reception areas
- Foyers

Product benefits

- Energy savings of up to 50 % compared to conventional luminaires
- Easy and quick installation
- Very homogenous light
- Very slim aluminum housing (only 10.5 mm) and matt white frame
- Certificates: CE

Product features

- Luminaire efficacy: up to 100 lm/W
- Luminous flux: 4,000 lm
- Available with color temperature: 3,000 K, 4,000 K
- Available with beam angle: 120°, 90° for UGR < 19 according to EN 12464-1
- Type of protection: IP20
- Aluminum housing, polystyrene diffuser
- Ambient temperature in operation: -10...+45 °C
- Lifetime: up to 50,000 h



Product datasheet

Technical data

Electrical data

Operating mode	Electronic control gear (EVG)
Nominal wattage	40.00 W
Nominal voltage	220...240 V
Mains frequency	50/60 Hz

Photometrical data

Color temperature	4000 K
Luminous flux	4000 lm
Light color (designation)	Cool White
Color rendering index Ra	>80

Light technical data

Beam angle	120 °
------------	-------

Dimensions & weight

Length	1195 mm
Width	295.0 mm
Height	10.5 mm

Colors & materials

Body material	Aluminum
Product color	White

Temperatures & operating conditions

Ambient temperature range	-10...45 °C
---------------------------	-------------

Capabilities

Dimmable	No
----------	----

Certificates & standards

Protection class	II
Type of protection	IP20

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
--------------	---------------------	---------------------------------	---	--------	--------------

Product datasheet

4058075807303	PANEL LED 1200 40 W 4000 K	Shipping carton box 4	1295 mm x 180 mm x 355 mm	82.75 dm ³	15200.00 g
---------------	-------------------------------	--------------------------	------------------------------	-----------------------	------------

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.