

## FEATURES

- **UV Resistant:** Ensures longevity and performance in outdoor environments
- **High Tensile Strength:** Supports up to 34 kg, providing robust cable management
- **UL 94 V-2 Fire Behaviour:** Offers flame retardancy for enhanced safety
- **Nylon Material:** Provides durability and resistance to wear
- **280 mm Length:** Suitable for a wide range of bundling applications
- **RoHS Compliant:** Meets environmental and safety standards

## RS PRO UV Protected Cable Tie, 280mm Nylon

RS Stock No: 656-117



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO UV Protected Cable Ties are designed for secure and reliable bundling of cables and wires. Made from durable nylon, they offer excellent resistance to UV exposure, making them ideal for outdoor applications. With a maximum bundle diameter of 70 mm, they provide flexibility for various cable management needs.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	UV Protected Cable Tie
Tensile Strength	34 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

### Mechanical Specifications

Length	280 mm
Material	Nylon
Maximum Bundle Diameter	70 mm
Width	4.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---