

Easykey Slim

Digital Handle

DOM



Keys or cards are not necessary thanks to its numeric and braille keyboard
Adaptable to almost any mortise lock on the market
Up to 150 user codes can be programmed

INTERAXIS	SPINDLE	DOOR THICKNESS	ARTICLE NUMBER
70	7	35	XS40SD7DL-10
70	8	35	XS40SD8DL-10
92	7	35	XS40SB7DL-10
92	8	35	XS40SB8DL-10
70	7	40	XS40SD7DL-20
70	8	40	XS40SD8DL-20
92	7	40	XS40SB7DL-20
92	8	40	XS40SB8DL-20
70	7	45	XS40SD7DL-30
70	8	45	XS40SD8DL-30
92	7	45	XS40SB7DL-30
92	8	45	XS40SB8DL-30
70	7	50	XS40SD7DL-40
70	8	50	XS40SD8DL-40
92	7	50	XS40SB7DL-40
92	8	50	XS40SB8DL-40

Dimensions in mm

Technical features

Material	Steel / Zamak
Finish	Stainless steel
Handle	L shape
Reversible	Yes
Interaxis	70 mm, 92 mm
Backset	22 mm and more
Door thickness	35 mm, 40mm, 45 or 50 mm
Spindle	7 or 8 mm
Fixation	5 screws
Battery type	Lithium battery, CR-P2 (6V)
Battery lifetime	40,000 cycles (Up to 3 years)
Low battery signal	Before last 500 openings
Light signals	Green / Red
Acoustic signals	Yes
Locking & opening time	The latch is locked automatically after 3 seconds
Master code	Yes
User code	With 4-6 digits Up to 150 user codes can be created
Security system	After 5 wrong codes, the lock is blocked for 1 minute
Memory information	EEPROM : user codes remain in memory when the battery is replaced
Backup	Cylinder override available
Functions	Change Master code Activate user code Deactivate user code Complete deactivation of all user codes Always free exit Optional : free entry function
Included accessories	Battery Fixation kit Mounting instructions
On request	Gold finish Spindle 9 mm Other door thickness Interaxis 72 and 85 mm U shape handle Renovation plate

Logistics



≈ 1,880 kg



Individual box