



115.111.129.98KGB0..-PP-ASLinear-Kugellager-Einheiten

Linear ball bearing and housing units

KGB020-PP-AS (Series KGB0..-PP-AS)

open design, sealed, greased, with relubrication facility;
corrosion-resistant design possible

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

Fw	20 mm
H	45 mm
B	70 mm
L	45 mm Tolerance: h12
	5 Number of rows of balls
1)	Main load direction
A3	21 mm
A5	35 mm Tolerance: +/-0,02
B1	45 mm
B2	10 mm Dimension B2 on diameter Fw
H2	25 mm Tolerance: +/-0,015
H6	8 mm
JB	58 mm Tolerance: +/-0,15
JL4	9,5 mm
K5	M6 For fixing screws to ISO 4762-8.8 If there is a possibility of settling, the screws should be secured against rotation.
K8	NIPA1 Lubrication nipple
L4	20 mm
L5	28 mm
N1	6,6 mm
N3	11 mm

α	60 °
m	0,25 kg Mass
C	1600 N Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.
C ₀	1280 N Basic load ratings in main load direction The basic load ratings are only valid for hardened (670 HV +165 HV) and ground shaft raceways.



