

# Circular Saw LXT®

## DHS710

18V X2 • 4 800 min<sup>-1</sup> • 190 mm

### Robust saw for heavy-duty professional use

A robust wood-cutting circular saw for professional use with two LXT® 18V batteries that offer an output of 36V. A solid aluminium table that can be tilted to an angle of 50°. A blade diameter of 190 mm that offers a maximum cutting depth of 68,5 mm. Compatible with a guide rule.



### Technical specifications

|                                            |                        |
|--------------------------------------------|------------------------|
| Nominal Battery Voltage                    | 2 x 18 V               |
| Voltage LXT                                | ✓                      |
| Max. Cutting Depth at 90°                  | 68,5 mm                |
| Max. Cutting Depth at 45°                  | 49 mm                  |
| Max. Cutting Depth at 50°                  | 44 mm                  |
| No load speed                              | 4800 min <sup>-1</sup> |
| Sound Power Level (L <sub>WA</sub> )       | 105 dB(A)              |
| Sound Pressure Level (L <sub>pA</sub> )    | 97 dB(A)               |
| Noise Uncertainty (K Factor)               | 3 dB(A)                |
| Tool weight with battery                   | 3,9 - 4,6 kg           |
| Product Dimensions (L x W x H):            | 356 x 217 x 298 mm     |
| Battery Chemistry (Ni-Cd / Ni-MH / Li-ion) | Li-ion                 |
| Max. Bevel Range (Right)                   | 0 - 50 °               |
| Blade Diameter                             | 190 mm                 |

### User benefits

- Rigid aluminium base provides smooth cutting thanks to its lightness, toughness and good bend resistance
- Battery protection system automatically shuts off power when the battery level is low
- The rubber coating on the handle ensures a firm working grip

Link to product - [www.makitauk.com](http://www.makitauk.com)



# Related products

## Other

User manual

Parts drawing