



Example image

CHARACTERISTICS

- Sendzimir galvanized

TECHNICAL DATA

Product material	Non-alloy steel 1.0215 E220 (EN 10305)
Surface roughness	10 µm
Thermal expansion	0.012 mm/(m·K)
Thermal conductivity, pipe	60 W/(m·K)

Specific thermal capacity 500 J/(kg·K)

ACCESSORIES

- Geberit Mapress pipe cutter R
- Geberit Mapress pipe deburrer
- Geberit Mapress insertion distance template with marker pen

Art. no.	DN	d _o mm	d _i mm	s mm	L m
These articles are suitable for the following system: Geberit Mapress Carbon Steel					
19402	12	15	12	1.5	6
19404	20	22	19	1.5	6
19405	25	28	25	1.5	6
19406	32	35	32	1.5	6

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
19407	40	42	39	1.5	6
19408	50	54	51	1.5	6
19409	65	76.1	72.1	2	6
19410	80	88.9	84.9	2	6
19411	100	108	104	2	6

These articles are suitable for the following system: **Geberit Mapress Carbon Steel (FKM blue)**

19402	12	15	12	1.5	6
19404	20	22	19	1.5	6
19405	25	28	25	1.5	6
19406	32	35	32	1.5	6
19407	40	42	39	1.5	6
19408	50	54	51	1.5	6
19409	65	76.1	72.1	2	6

Art. no.	DN	d _ø mm	d _i ø mm	s mm	L m
19410	80	88.9	84.9	2	6
19411	100	108	104	2	6