

**BOSCH**

Invented for life

Power tools for trade &amp; industry

## Product data sheet



Cordless Angle Grinder

### GWS 10,8-76 V-EC

Satisfaction guaranteed - the most manageable small angle grinder

#### The most important data

Battery voltage	10,8 V
No-load speed	19.500 rpm
Grinding/cutting disc, diameter	76 mm

**Part number:** 0 601 9F2 000**GBP 99,00\***[> More product information](#)*\* Recommended retail price excluding VAT*

#### Technical data

Battery capacity	2,5 Ah
No-load speed	19.500 rpm
Battery voltage	10,8 V
Grinding spindle thread	M5
Bore size, diameter	10,0 mm
Weight incl. battery	0,9 kg
Length	202,0 mm
Width	88,0 mm
Height	105,0 mm
Tools	
Grinding/cutting disc, diameter	76 mm

#### Noise/vibration information





Surface grinding (roughing)	
Vibration emission value ah	13.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



Power tools for trade & industry

**Advantages:**

- Handy in every situation - extremely compact and ergonomic for fast disconnection on the construction site
- Fast work rate thanks to the high-performance EC motor
- Highly versatile for different materials
- The first 10.8 volt angle grinder
- Easy to swap discs thanks to the new spindle lock
- Easy adjustment of the protective cover without having to use tools



**Prices / Scope of delivery**

Part number	<b>0 601 9F2 000</b>
1x carbide cutting disc Carbide Multi Wheel 2 608 623 011	✓
2x cutting discs Expert for Inox 2 608 601 520	✓
Carton (L-BOXX-ready)	✓
L-BOXX inlay 1/2 1 600 A00 F0F	✓
<b>Price</b> (Recommended retail price excluding VAT)	<b>GBP 99,00</b>